

:: BLEED ROLLER METAL FLEXI

Description:

Is a plastic venting roller for venting polyester or epoxy laminates, among others. It exists in different types and sizes.

Available in the following dimensions:

Plastic disc roll	Diameter of	12 mm , width of	50 mm
		12 mm	100 mm
		40 mm	8 mm
Aluminium disc roller		12 mm	35 mm
		12 mm	140 mm
Aluminium crosscut		21 mm	140 mm
		45 mm	225 mm
metal flexi roller		25 mm	90 mm
		40 mm	130 mm

Application:

For the proper venting of glass fibre, carbon and aramid laminates, among others. Solvent resistant.

Data on delivery:

Color:	not applicable
Viscosity:	not applicable
Mass density:	not applicable
Shelf life:	unlimited
Consistency:	fixed

Technical data:

Consumption:	not applicable
Shore:	not applicable

Processing:

After impregnating the glass mat, you should use a de-aeration roller to remove the air bubbles. Roll this with light pressure over the still wet glass-resin combination until the air bubbles have disappeared.

Note: clean the vent roller each time after use to avoid it becoming jammed due to the hardening of the resin.

Safety:

Is not a dangerous product.